

SERIES AZ 1400T TIED DIAPHRAGM REGULATOR

Intermediate to high flow applications

- Single stage
- SS 316L construction
- Absolute sub-atmospheric option, flow rate to 6 slpm
- Cylinder or point of use specialty and bulk gases
- Flow rates to 600 slpm (21 scfm)
- Vacuum to 2,300 psig (159 bar) inlet HR option to 3,000 psig (207 bar)
- Knob LOTO (refer to AP KL data sheet)
- Installation and operating instructions available at <u>www.aptech-online.com</u> in the Tech Briefs section

Operating Parameters

Source pressure	AZ 1400T AZ 1400TA AZ 1400T HR	vacuum to 2,300 psig (159 bar) vacuum to 300 psig (21 bar) vacuum to 3,000 psig (207 bar)
Delivery pressure		100 mm Hg absolute to 30 psig (2 bar) (not available for HR)
	AZ 1402T	1 to 30 psig (0.07 to 2 bar) (not available for HR)
	AZ 1406T	1 to 60 psig (0.07 to 4 bar) (not available for HR)
	AZ 1410T	2 to 100 psig (0.14 to 7 bar)
	AZ 1415T*	5 to 150 psig (0.34 to 10 bar)
Proof pressure		150% of operating pressures
Burst pressure		300% of operating pressures

*AZ 1415T will not achieve full outlet pressure rating at all inlet pressures.

Other Parameters

Inlet/outlet connectors	1/4, 3/8 or 1/2 inch face seal or tube weld		
Flow coefficient (Cv)***	0.5		
Internal volume	1.06 in ³ (17.4 cm ³)		
Operating temperature	-40° to +160°F (-40° to +71°C)**		
Surface finish	10 μin. (0.25 μm) Ra avg. standard		
	25 μin. (0.62 μm) Ra avg. optional		
Inboard leakage	2 x 10 ⁻¹⁰ sccs		
Outboard leakage	2 x 10 ⁻⁹ sccs He		
Leakage across seat	4 x 10 ⁻⁸ sccs He		
Installation	surface or panel (optional)		
Supply pressure effect	1.6 psig per 100 psig source pressure change		

**VS option 14° to 194°F (-10° to + 90°C).

***A pressure regulator Cv is a nominal value which indicates the point of choked flow. Please refer to a flow curve or a recommendation guide for usable flow range.

Materials


	Series AZ 1400T S
Wetted Parts	
Body, nozzle	stainless steel 316L***
Diaphragm, poppet	Ni-Cr-Mo alloy / UNS N06022
Finish	electropolished and passivated
Seat	PCTFE (Polyimide optional)

***Please refer to product note PN 414 regarding single melt 316L SS material.

All specifications subject to change without notice.



ULTRACLEAN BY DESIGN



CAUTION: Product selection is the sole responsibility of the user, regardless of any recommendations or suggestions made by the factory. The user shall make selections based upon their own analysis and testing with regard to function, material compatibility and product ratings. Proper installation, operation and maintenance are also required to assure safe, trouble free performance.

Top View

0 1 2

3 4 5

6 7 8 9 10

Flow Rate in SLPM of Nitrogen

Sample Order Number	AZ 1402TSQA 3PW FV4 FV4 V3		
AZ 1402T Series	AZ 1402T = 1-30 psig (.07 to 2 bar) AZ 1406T = 1-60 psig (.07 to 4 bar) AZ 1410T = 2-100 psig (.14 to 7 bar) AZ 1415T = 5-150 psig (.35 to 10 bar)	FV4 FV4 Connections Inlet / Outlet	FV4 = 1/4 inch face seal female MV4 = 1/4 inch face seal male FV6 = 3/8 inch face seal female MV6 = 3/8 inch face seal male FV8 = 1/2 inch face seal female
S Material	S = Stainless steel (SHP)* *S equivalent to SHP – stainless steel with Ni-Cr-Mo alloy poppet and diaphragm		MV8 = 1/2 inch face seal male Tube weld stub available
Q Surface Finish Option	$Q = 25 \mu in. Ra avg.$	V3 Gauges** Source / Delivery	0 = No gauge V3 = 30-0-30 psig/bar L = 30-0-60 psig/bar 1 = 30-0-100 psig/bar
A Range Options	A = 100 mm Hg absolute to 30 psig (2 bar) (AP 1402T option only)		2 = 0-200 psig/bar 4 = 0-400 psig/bar 10 = 0-1000 psig/bar 40 = 0-4000 psig/bar
3PW Ports	2PW = 2 ports butt weld 3PW = 3 ports butt weld 4PW = 4 ports butt weld	le e	**Standard gauge ports are 1/4 inch face seal male (1/4 inch face seal female are available)
	ns and variations which are not documented in nodel number that is not defined by the ordering	***Panel hole 1.56" diameter.	VS = Polyimide seat HR = High inlet pressure P = Panel installation***

data sheets. If you have a model number that is not defined by the ordering information, please consult the factory or your local representative.

KL = Knob LOTO (refer to AP KL data sheet)

OUTLET PRESSURE (BAR)

OUTLET PRESSURE (BAR)

OUTLET PRESSURE

(mm Hg Absolute)

Bottom View